

Perfect washing and drying

Every detail has been optimized and designed to ensure the best performance!

Thermal disinfection is the most recommended and effective method for disinfecting dental devices. Thermal disinfection is required to comply with any legal provision between different countries.

To ensure the best possible results, the AWD655 line is also equipped with an efficient hot air drying system that facilitates the total elimination of residual water both inside and outside the dental instruments.

State-of-the-art glassware washers for innovation and technological process

AWD655 glassware washers are an important washing and cleaning aid in the laboratory, life sciences and pharmaceutical industries. They guarantee the operator washing results with analytical purity, tested and constantly efficient.

The glassware washers have a large load capacity, laboratory glassware is available quickly and peak loads can be disposed of more quickly.

Thanks to the large variety of modular racks, inserts and accessories, the glassware washers ensure maximum flexibility, since the racks can be intuitively combined in a different way every time.

The washing programs adapt to any type of dirt and glassware and the quantity of objects to be treated.